

Product: GPS1-KSZ9HH

Configurator: GPS1-KSZ9HH



Configurator Description

GREYHOUND power supplies, available in high- or low-voltage options, can be changed in the field.

Technical Specifications

Product description

Description	Power supply GREYHOUND Switch only
Part Number	942136002
Configurator Part Number	942136999

Power requirements

Operating Voltage	60 to 250 V DC and 110 to 240 V AC
Power consumption	2.5 W
Power output in BTU (IT)/h	9

Ambient conditions

MTBF (MIL-HDBK 217F: Gb 25 °C)	757 498 h
Operating temperature	0+60 °C
Minimum Storage Temperature	-40+70 °C
Relative humidity (non-condensing)	5-95 %

Mechanical construction

Weight	710 g
Protection class	IP30

Mechanical stability

IEC 60068-2-6 vibration	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD)	8 kV contact discharge, 15 kV air discharge
EN 61000-4-3 electromagnetic field	35 V/m (80-2700 MHz); 1 kHz, 80% AM
EN 61000-4-4 fast transients (burst)	4 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line); data line: 1 kV; IEEE1613: power line 5kV (line/earth)
EN 61000-4-6 Conducted Immunity	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
EN 61000-4-16 mains frequency voltage	30 V, 50 Hz continuous; 300 V, 50 Hz 1 s

EMC emitted immunity

EN 55032	EN 55032 Class A
----------	------------------

Approvals

Safety of industrial control equipment	EN61131, EN60950
--	------------------

Reliability

Guarantee	60 months (please refer to the terms of guarantee for detailed information)
-----------	---

Scope of delivery and accessories

Accessories	Power Cord, 942 000-001
Scope of delivery	Device, General safety instructions

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.