



Product: [REVConnect Panel 24P](#) 

RVMPPF1U24-REVConnect Patch Panel, Empty, Flat, 1U, 24P, UTP

Product Description

REVConnect Patch Panel, Empty, Flat, 1U, 24 Ports

Technical Specifications

Product Overview

Suitable Applications:	For use with REVConnect Modular Jacks
------------------------	---------------------------------------

Physical Characteristics (Overall)

Overall Height:	1.730 in
Overall Width:	19.000 in
Overall Depth:	2.000 in
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	1.370 lbs.

Connectors

Materials

Description	Material	Color
Panel	Steel	Black/White
Frame	PC/ABS	Black/White
Management Bar	Steel	Black
Clear Window	Polycarbonate	Transparent

Construction and Dimensions

Max Capacity:	24 Connectors
---------------	---------------

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Connector System Compatibility:	KeyConnect
---------------------------------	------------

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	REVConnect Modular Jacks, REVConnect 10GXS, 10GXW, 3600, 2400, 1200 Systems
----------------	---

Variants

Item #	Color	UPC
RVMPPF1U24BK	Black	611589238045

Product Notes

Included Parts:	4 Frames; 4 Clear Windows; 1 Label Card; 1 Rear Cable Management Bar; 4 Screws (10x32); 4 Screws (12x24); 2 Velcro Straps; 2 Installation Guides (English and French)
Notes:	For proper installation, refer to Installation Guide PX106520 included with the product, or visit our website at http://www.belden.com

History

Update and Revision:	Revision Number: 0.93 Revision Date: 12-03-2025
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.