
OA172SAP IP55 Series

AC Fans - 115, 230V
172mm x 150mm x 51mm (6.8” x 5.9” x 2.0”)





Frame	Die Cast Aluminum, Black Painted
Impeller	PBT, UL94 V-0 Plastic
Connection	2x Terminals
Motor	Capacitor Induction, Single Phase, Auto Cutoff, Auto Reset, Thermally Protected, Class B Insulation, IP55 Rated
Bearing System	Dual Ball Bearings
Dielectric Strength	1500VAC/min, <5mA
Insulation Resistance	≥100MΩ @ 500 VDC


Operating Temperature
-20°C ~ +70°C

Storage Temperature
-40°C ~ +100°C

Life Expectancy
40,000 Hours (L10 at 40°C)

Installed Options
IP55 Rated Motor

Weight: 2.7 lbs.



Model Number	Part Number	Rated Voltage (Volts AC)	Voltage Range (Volts AC)	Frequency (Hertz)	Rated Current (Amps)	Locked Current (Amps)	Input Power (Watts)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ($"H_2O$)
OA172SAP-11-1TBIP55	230315302	115	103 ~ 126	50 / 60	0.25	0.43	31	3400	226	58	0.79
OA172SAP-22-1TBIP55	230615302	230	207 ~ 253	50 / 60	0.12	0.19	29	3400	226	58	0.79

* 60Hz Performance values shown in table.

Knight Electronics, Inc.
10557 Metric Drive
Dallas, TX 75243
214-340-0265

Revised 6/15/2026
m2

E170149

Orion Fans
Information and data is subject to change without prior notification