

Amp Signal Conditioner

For Direct AC and DC Current Measurement



0-5A Direct
AC/DC Auto-Detect

1%
Accuracy



Remote monitoring
with **APM Gateway** and
Trumeter Cloud



2 Outputs
Digital (open collector) or
Analog (4-20mA)




DIN Rail Mount
Compact design for
simple installation



10 alarm set points



User-configurable
settings via the free,
easy-to-use software



True RMS

Less than 62mm deep

The Amp Signal Conditioner is designed to accurately measure AC and DC currents up to 5 A with 1% precision, automatically detecting the input type for seamless operation. It ensures reliable current monitoring, making it ideal for industrial equipment, power supplies, energy management, automation systems, and laboratory testing. By handling multiple current types in a single device, it simplifies system design and enhances measurement efficiency across diverse applications.

Designed for DIN rail mounting, the unit combines precision with versatility, with user-configurable scaling and settings, making it suitable for a wide range of industrial environments. It integrates seamlessly with other control and monitoring systems through configurable digital and analog outputs.

For extended functionality, the Amp Signal Conditioner can be paired with the APM Gateway to connect directly to Trumeter Cloud. This secure connection enables remote monitoring, data logging, and alerts via email or online dashboard, with SMS alerts available as an option. Unlocking full visibility and actionable insights into system performance anytime, anywhere.


Go to www.trumeter.com for further information

Programmable

Simply connect to any USB port on your PC, launch the free configurator software, and start configuring.

- Scale (offset, gain and linear) and Range (min and max).
- 20 point non-linearization scaling for non-linear sensors.
- Ten independent alarm set-points.
- Configurable digital output delays (control the time output stays open/closed - .5 seconds – 120 seconds).

Dimensions



INSTALLATION: Standard 35mm
Top Hat Slotted (TS35) DIN rail

Specification

INPUT

Range	0-5A AC/DC
Max with CT	10,000A
Accuracy	1%

ENVIRONMENTAL

Temperature - operating	-10 to +60°C
Temperature - storage	-40 to +70°C
IP rating	IP20

POWER SUPPLY

Nominal Input	12-24VAC or DC
---------------	----------------

OUTPUTS

Max voltage	34V
Max current	500mA
Analogue output	4-20mA



CERTIFICATION

UL, cUL, CE

Part Numbers

SC-AMP-DIN	Amp Signal Conditioner, DIN Rail Mount
022128-01	USB Cable

We can **customize** our **Signal Conditioners** to match your requirements, adding extra **functionality** or **communication protocols** to suit your needs. If you can't find what you're looking for, **ask about our custom solutions!**



www.trumeter.com

Trumeter (The Americas)
6601 Lyons Rd, Suite H-7
Coconut Creek, Florida
FL 33073,
USA
Tel: +1 954 725 6699
Email: sales.usa@trumeter.com

Trumeter (Europe)
Trumeter
Pilot Mill, Alfred Street
Bury, Lancashire
BL9 9JR
Tel: +44 161 674 0960
Email: sales.uk@trumeter.com

Innovative Design Technologies Sdn. Bhd.
Lot 5881, Lorong Iks Bukit Minyak 1
Taman Perindustrian Iks, 14000 Bukit Tengah
Penang, Malaysia
Web: www.idtworld.com
Tel: +604 5015700
Email: sales.my@idtworld.com