








APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/27/10	
A		REDRAWN	10/2/14	HR/LL



RECOMMENDED PCB LAYOUT



ASSEMBLY VIEW

PACKAGED ON TAPE & REEL

Positions: 02 thru 16 and 18, 20, 22, 24, 26, 28, 30
A = .049 [1.25] x No. of Spaces
B = .049 [1.25] x No. of Spaces + .252 [6.40]
C = .049 [1.25] x No. of Spaces - .049 [1.25]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .049 [1.25] WAFER, SMT, RIGHT ANGLE

TIN PLATED

Electrical:
Operating voltage: 100 VAC/DC max
Current rating: AC/DC 1 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 100 Mohms min
Dielectric withstanding voltage: 250 VAC for 1 minute
Mechanical:
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH			
INCHES				909 Rahway Avenue, Union, NJ 07083			
HOLES				Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	Ø.X	± .10	TITLE .049 [1.25] WATER, SMT, RIGHT ANGLE			
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	DY	7/27/10		SIZE PART NO. TIN PLATED			
CHECKED							
APPROVED							
REF:	S00123T	SCALE:	NTS	SHEET	1 OF 1	REV.	A