


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED DRAWING	2/21/17	HR/CH
B		UPDATED DRAWING	6/4/19	AY/IL



RECOMMENDED PCB LAYOUT
Applicable PC Board T=0.8~1.6mm

Positions: 02 thru 15, 20, 25, 30

A= .049 [1.25] x No. of Space

B= .049 [1.25] x No. of Positions + .026 [0.65]

C= .049 [1.25] x No. of Positions + .049 [1.25]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Beige

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 250V AC/DC

Current rating: 1A AC/DC

Contact resistance: 10 mohms max Initial
30 mohms max After

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010						
APPROVALS			DATE		TITLE 1.25MM PITCH WAFER, DIP TYPE, RIGHT ANGLE, TIN PLATED	
DRAWN		BW	01/17/07			
CHECKED						
APPROVED						
REF: S00099T			SCALE: NTS		SHEET 1 OF 1	