





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9507	RELEASED	4/29/09	
A		UPDATE DRAWING	10/13/14	HR/NP



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Nylon 66, rated UL 94V-0
Insulator color: Beige
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VDC max
Current rating: AC/DC 1 Amp max
Contact resistance: 30 mohms max
Insulation resistance: 1,000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 15, 20, 25, 30
A = .049 [1.25] x No. of Spaces
B = .049 [1.25] x No. of Positions + .026 [0.65]
C = .049 [1.25] x No. of Positions + .049 [1.25]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØXX	± .10	TITLE .049 [1.25] SHROUDED HEADER STRAIGHT, PCB			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN				DY			
CHECKED				4/29/09			
APPROVED				X			
SIZE				PART NO.			
REF: S00099T				125SH-C-XX-TS			
SCALE: NTS				REV. A			
SHEET 1 OF 1							