





6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/08/09	
A		UPDATE DIM. & SPEC.	2/10/20	AY/RC
B		UPDATE DIM. & SPEC.	2/22/21	LH/EY
C		UPDATE DIM. & SPEC.	2/24/21	LH/EY



SECTION A-A



SECTION B-B

A

SPECIFICATIONS:

Material:

Contact: Phosphor Bronze, Thickness= 0.20mm

Plating:

Tin over Copper underplate overall

Electrical:

Wire range: 24-28 AWG

Insulation O.D: 1.70mm (max)

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS DATE

DRAWN	DY	6/08/09
-------	----	---------

CHECKED		
---------	--	--

APPROVED		
----------	--	--

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

2.50MM PITCH CRIMP TERMINAL

SIZE

X

PART NO.

25CTC-R

REV.

C

REF: S00016T

SCALE: NTS

SHEET 1 OF 1