






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/24/16	



SECTION A-A



SECTION B-B

SPECIFICATIONS:
 Material: Brass
 Plating: Tin Plated
 Thickness: 0.20mm
 Wire Range: AWG#24~#28
 Insulation O.D: 1.10~1.50mm
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		TITLE	
DRAWN	AY	2/24/16		.079" [2.00] PITCH MALE TERMINAL	
CHECKED	TW	2/24/16		FOR P/N: 2CH-YL-XX	
APPROVED				SIZE X	PART NO. 2CTYL-R
				REF: S00016T	SCALE: NTS
				SHEET 1 OF 1	