





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/16/04	
A		REVISED SPEC.	5/17/11	



SPECIFICATIONS:
Material: Nylon 66, rated UL 94V-2
Insulator color: Natural
Contacts: Brass

Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 7 Amps max
Insulation resistance: 1000 Mohms min
Dielectric withstanding voltage: 1500 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant.

A = .165 [4.20] x No. of Spaces + .205 [5.20]
B = .165 [4.20] x No. of Spaces
C = .165 [4.20] x No. of Spaces + .370 [9.40]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X ± .10 .XX ± .020 .XXX ± .015	Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010			909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE			
DRAWN SS		9/16/04		STRAIGHT HOUSING, MALE TERMINAL PCB MOUNT WITH PEGS			
CHECKED				SIZE		PART NO.	
APPROVED				X		DMF-XX-S-P	
REF: S00016T	SCALE: NTS	SHEET 1 OF 1	REV: A				

A

B

C

D

A

B

C

D

6

5

4

3

2

1

6

5

4

3

2

1

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____


Rev AWO # Description Date Appr

SEE SHT 1 OF 2 FOR REVISION


D

D


2 POSITION




8 POSITION



14 POSITION




20 POSITION




C

C


4 POSITION




10 POSITION



16 POSITION




22 POSITION




B

B


6 POSITION




12 POSITION



18 POSITION



24 POSITION



A

A

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE STRAIGHT HOUSING, MALE TERMINAL
PCB MOUNT WITH PEGS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS:		DATE	
DRAWN	SS	9/16/04	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	DMF-XX-S-P	A	
REF:	SCALE: NTS	SHEET 2 OF 2	

6

5

4

3

2

1