

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/10	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

Unit: Inch / mm

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Contacts: Phosphor Bronze

Shell: Steel, Tin plated

Hardware: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 235°C for 5 seconds

Positions

Positions	DIMENSIONS			
	A	B	C	D
9	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]
15	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]
25	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]
37	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]
50	2.064 [52.43]	2.406 [61.11]	2.637 [67.00]	2.169 [55.10]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

D-SUB SOCKET, STANDARD PROFILE

.118 [3.00] THRU-HOLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE	
INCHES				D-SUB SOCKET, STANDARD PROFILE	
HOLES				.118 [3.00] THRU-HOLE	
.X ± .10 ØX ± .10					
.XX ± .020 ØXX ± .015					
.XXX ± .015 ØXXX ± .010					
APPROVALS				DATE	
DRAWN				5/11/10	
CHECKED					
APPROVED					
SIZE				PART NO.	
X				DXXX-ST-1-MC	
REF:				SCALE: NTS	
				SHEET 1 OF 1	



6

5

4

3

2

1