





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/20	
A		UPDATE DRAWING	4/7/21	LH/RC



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Screw: M2.5

Contact: Copper Alloy, Tin plated.

Electrical:

Voltage rating: 300 VAC

Current rating: 12 Amp

Dielectric withstanding voltage: 1,600 VAC for 1 minut

Mechanical:

Torque: 0.4Nm

Wire Range: 26-14 AWG

Wire strip length: 5~6mm

Environmental:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Poles: 2 thru 24

A = .200 [5.08] X No. of Positions

B = .200 [5.08] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	LH	11/12/20
CHECKED	RC	11/12/20
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	
EURO BLOCK, .200 [5.08] PITCH, 45 DEGREE ANGLE	
SIZE	PART NO.
X	EB21A-XX-D-DA
REV.	A
REF:	S00067C
SCALE:	NTS
SHEET	1 OF 1