








APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/05	
A		CHANGE TERMINAL	8/15/08	
B		REDRAWN	3/12/09	SS
C		UPDATED MARKINGS	12/18/12	SS
D		REVISED SPEC.	12/20/12	
E		REDRAWN	12/20/12	
F		ADDED MARKING	10/12/18	AY/RC



PANEL THICKNESS	DIMENSIONS	
	A	
.031-.071 [0.80-1.80]	1.240	[31.50]
.075-.126 [1.90-3.20]	1.248	[31.70]

TERMINAL OPTIONS		
-1	-2	-3
.187 Q.C.	.250 Q.C.	.157 Solder

SPECIFICATIONS:

Material:
Insulator: Nylon 66, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC
Current rating: UL & CSA: 15 Amp
ENEC: 10 Amp
Insulation resistance: 100 Mohms min @ 500 VDC
Dielectric withstanding voltage: 3,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 ØX ±.10 .XX ±.020 ØXX ±.015 .XXX ±.015 ØXXX ±.010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS					TITLE	
DRAWN		SS	6/17/05		IEC MALE INLET, SNAP-IN PANEL MOUNT 5 x 20mm FUSE HOLDER	
CHECKED						
APPROVED		SS	3/17/09			
REF:		S00087C		SCALE: NTS		SHEET 1 OF 1