





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/13/07	
A		REVISED DIM.	8/17/12	



PCB LAYOUT



SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-2
Insulator color: White
Contacts: Brass
Plating: Gold Flash over Nickel underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating: -40°C to +105°C
Environmental:
Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES			TITLE	RIGHT ANGLE, PCB, HI-TEMP, GOLD PLATED		
.X ± .10	ØXX ± .10			.100 [2.54] LOCKING HEADER			
.XX ± .020	ØXXX ± .015						
.XXX ± .015	ØXXX ± .010						
APPROVALS	DATE						
DRAWN	SS	7/13/07		SIZE	PART NO.	LHA-XX-GR4	REV.
CHECKED				X			A
APPROVED				REF:	S00123T	SCALE: NTS	SHEET 1 OF 1