



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/10/09	
A		ADDED DRAWING	12/25/18	AY/RC1






60, 64 PIN




20, 24, 26, 30, 34, 40, 50 PIN



10, 14, 16 PIN



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0, Color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 1 Amp
Contact Resistance: 10 mohm max
Insulation resistance: 1000 Mohm min
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant.



Positions: 10, 14, 16, 20, 24, 26, 30, 34, 40, 50, 60, 64
A = .100 [2.54] x No. of Spaces + .855 [21.71]
B = .100 [2.54] x No. of Spaces + .454 [11.54]
C = .100 [2.54] x No. of Spaces
D = .100 [2.54] x No. of Spaces + .305 [7.74]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	12/10/09
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
LATCH BOX HEADER, RIGHT ANGLE
LONG EJECTOR LATCHES

SIZE	PART NO.	REV.P
X	MHR-XX-HUAL	A
REF: S00059T		SCALE: NTS
		SHEET 1 OF 1