






Rev	AWO #	Description	Date	Appr
-		RELEASED	3/16/05	
A		REVISED SPEC.	12/15/10	
B		REDRAWN	12/22/10	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Natural
Contacts: Phosphor Bronze
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 200 VAC max
Current rating: 1 Amp max
Contact resistance: 20 mohms max initial
Insulation resistance: 500 Mohms min
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +85°C
Environmental:
Lead free, RoHS compliant

Positions: 3 thru 32

A = .049 [1.25] x No. of Spaces
B = .049 [1.25] x No. of Spaces + .106 [2.70]
C = .049 [1.25] x No. of Spaces + .278 [7.05]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

ZIF FLEX CIRCUIT CONNECTOR

TOP ENTRY, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			TITLE		
INCHES			ZIF FLEX CIRCUIT CONNECTOR		
Holes			TOP ENTRY, PCB		
.X ± .10	Ø.X	± .10			
.XX ± .020	Ø.XX	± .015			
.XXX ± .015	Ø.XXX	± .010			
APPROVALS			DATE		
DRAWN			3/16/05		
SS					
CHECKED					
APPROVED					
SIZE			PART NO.		
X			PCA-1-XX-V-3-20		
REF: S00030T			SCALE: NTS		
			SHEET 1 OF 1		
			REV. B		

