






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/29/23	



THICKNESS OF PANEL IS
FROM 0.8mm TO 1.2mm
RECOMMENDED PANEL CUT



L: 2x0.3mH
Cx 0.1uF(X2)
Cy 3300pF(Y2)

SPECIFICATIONS:

Electrical:

Voltage rating: 115/250 VAC

Current rating: 115/250 VAC: 10A RMS max

Operating frequency: 50/60Hz

Leakage Current: Each Line To Ground

@115VAC/60Hz 0.4mA max

@250VAC/50Hz 0.8mA max

Hipot Rating(For 1 Minute)

A. Line to Ground: 2,250 VDC

B. Line to Line: 1,450 VDC

IR: 50 Mohm @500 VDC Any Input or Output to Ground

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES
.X	± .10	ØX ±.10
.XX	± .020	ØXX ±.015
.XXX	± .015	ØXXX ±.010

DRAWN	WX	5/29/23
CHECKED	RC	5/29/23
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710


TITLE FILTERED POWER ENTRY MODULE, W/ SWITCH 115/250V AC, 10A, SNAP IN PANEL MOUNT		REV. -
SIZE X	PART NO. PLF-11B3-10A-Q	
REF: S00205C	SCALE: NTS	SHEET 1 OF 2

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				

INSERTION LOSS(IN 50 ohm system according IEC/CISPR



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED		
INCHES		HOLES
.X	± .10	ØX ±.10
.XX	± .020	ØXX ±.015
.XXX	± .015	ØXXX ±.010
DRAWN	WX	5/29/23
CHECKED	RC	5/29/23
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		

ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
TITLE FILTERED POWER ENTRY MODULE, W/ SWITCH 115/250V AC, 10A, SNAP IN PANEL MOUNT			
SIZE X	PART NO. PLF-11B3-10A-Q		REV. -
REF: S00205C	SCALE: NTS	SHEET 2 OF 2	