



Rev	AWO #	Description	Date	Appr
-		RELEASED	7/01/08	

654321

APPROVED: _____

DATE: _____ TITLE: _____




12	NUT	ZINC	NICKEL	1
11	WASHER	BRASS	NICKEL	1
10	RUBBER WASHER	RUBBER	RED	1
9	WASHER	BRASS	NICKEL	1
8	CENTER CONTACT	BRASS	GOLD	1
7	BODY	ZINC	NICKEL	1
6	WASHER	FE	NICKEL	1
5	SPRING	65MN		1
4	DUT CONTACT	ZINC ALLOY	NICKEL	1
3	RUBBER WASHER	PVC	RED	1
2	SHELL	ZINC	NICKEL	1
1	INSULATOR	ABS		1
NO	DESCRIPTION	MATERIAL	FINISH	QTY

SPECIFICATIONS:

Electrical:

Nominal Impedance: 75 ohms
Frequency range: 0–4 GHz
Maximum peak voltage: 500V
Insulation resistance: 5000 Mohm min @ 500 VDC
Dielectric withstanding voltage: 1500 VAC rms
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Ratway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC MALE CLAMP RG59U, 75 OHM

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

APPROVALS	DATE
DRAWN DY	7/01/08
CHECKED	
APPROVED	

BNC MALE CLAMP RG59U, 75 OHM

SIZE	PART NO.	REV.
X	RF1-50-D-04-75	-
REF:	SCALE: NTS	SHEET 1 OF 1