

6

5

4

3

2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev

AWO #

Description



Date

Appr


-

RELEASED


11/23/18



RECOMMENDED PANEL CUT



SD-PNLXX-FFTRH-P00-000



## SPECIFICATIONS:

## Material:

Housing: Nylon 46, Color: Black  
 Contacts: Brass, Gold Flash over Nickel  
 Shell: Zinc Alloy, Nickel plated  
 O-ring: EDPM, Color: Black  
 Nut: Brass, Nickel plated  
 Washer: Brass  
 Environmental:  
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES

.X  $\pm .10$   $\phi .X$   $\pm .10$   
 .XX  $\pm .020$   $\phi .XX$   $\pm .015$   
 .XXX  $\pm .015$   $\phi .XXX$   $\pm .010$

APPROVALS

DATE

DRAWN

HR

11/23/18

CHECKED

AC

11/23/18

APPROVED

**ADAM**  
**TECH**  
**INTERCONNECTS**

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

TITLE

WATERPROOF CONNECTOR, FEMALE, M8 DIN,  
 REAR PANEL, SCREW MOUNT, STR PCB TYPE

SIZE

X

PART NO.

SD-PNLXX-FFTRH-P00-000

REV.

-

REF: S00200T

SCALE: NTS

SHEET 1 OF 1