


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/21/12	
A		REDRAWN	10/24/13	AY/SS
B		REVISED SPEC.	4/10/14	AY/KW

APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating: 15u" Gold over Nickel underplate on contact area, Tin over Nickel underplate on SMT tails

Electrical: Contact resistance: 20 mohms max. initial Dielectric withstanding voltage: 300 VAC for 1 minute

Temperature Rating: Operating temperature: -40°C to +85°C

Environmental: Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DRAWN	AY	6/21/12
CHECKED	CC	6/21/12
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

SMALL FORM FACTOR CONNECTOR, 20P
SMT TYPE, 15u" SEL GOLD PLATED

REV. B

SCALE: NTS

SHEET 1 OF 1