


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/16	



SPECIFICATIONS:

Material:
 Insulator: Nylon 66, rated UL 94V-0
 Insulator color: Black
 Screws: M3.5 Steel, Nickel plated
 Pin header: Brass, Nickel plated
 Electrical:
 Operating voltage: 300 V
 Current rating: 25 A
 Contact resistance: 20 mohms max.
 Insulation resistance: 1000 Mohms min. @ 500 VDC
 Dielectric withstanding voltage: 2,000 VAC for 1 minute
 Mechanical:
 Wire range: 22-12AWG, 4.0mm²
 Torque: 0.8N-m, 7.0Lb-in
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



1 Poles = 2 Screws (TDB-02-HB = 4 Screws)
 Positions: 2 thru 26
 A = .433 [11.00] x Spaces + 1.197 [30.40]
 B = .433 [11.00] x Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		TITLE .433 [11.00] DUAL ROW BARRIER BLOCK HIGH BODY	
HOLES		SIZE X	PART NO. TDB-XX-HB
APPROVALS		DATE	REV. -
DRAWN	AY	4/8/16	
CHECKED	LL	4/8/16	
APPROVED			
REF: S00067C		SCALE: NTS	SHEET 1 OF 1