

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/02/10	
A		UPDATED SPECS	1/28/13	
B		ADDED SPEC.	6/12/14	HR/JAY
C		UPDATED DRAWING	11/27/14	HR/LL
D		UPDATED DRAWING	5/19/17	SS



Common terminal shared
between 2 screws

1 Poles = 2 Screws

Poles	ADAM P/N
2	TDJ-04
3	TDJ-06
4	TDJ-08
5	TDJ-10
6	TDJ-12
7	TDJ-14
8	TDJ-16
9	TDJ-18
10	TDJ-20
11	TDJ-22
12	TDJ-24

L = .571 [14.50] x No. of (Pole-1) + .441 [11.20]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Terminal: Brass, Nickel plated

Wire protector: Stainless Steel

Screws: Steel, Zinc plated

Electrical:

Operating voltage: 600 V max

Current rating: 65 A max

Insulation Resistance: 500 Mohms min @ 500 VDC

Dielectric Withstanding Voltage: 2,000 VAC for 1 min.

Mechanical:

Suitable Electric Wire: 20-6 AWG

Recommended Screw Torque: 12.2 Lbf/inch

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

TERMINAL BLOCK, DUAL ROW, 14.50mm PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		Holes	
.X	± .10	ØX	± .10	.XX	± .020
.XX	± .020	ØXX	± .015	.XXX	± .015
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE		DATE	
DRAWN	DY	3/02/10			
CHECKED					
APPROVED					
SIZE		PART NO.		REV.	
X		TDJ-XX		D	
REF: S00026C		SCALE: NTS		SHEET 1 OF 1	