






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/21	



SPECIFICATIONS:

Material:

Cage: Copper Alloy

Electrometric Gasket: Conductive Rubber

Cage Rear EMI Gasket: Conductive Foam

Front Flange: Zinc Alloy, Nickel plated

Front EMI Gasket: Copper Alloy, Matte Tin over Nickel underplate overall

Heat Sink Clip: Copper Alloy

Heat Sink: Aluminum, Nickel plated

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	mm	Angles
.X	± .25	± 2°
.XX	± .13	
.XXX	± .10	

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH





**ADAM
TECH**

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT DIP TYPE, PRESS FIT, EMI CLIP W/ GASKET, W/ HEAT SINK	
SIZE	PART NO.	REV.	
X	XFC-1-CS2-EMI-PF-HSK	-	
REF:	S00005C	SCALE:	NTS
SHEET		1 OF 3	

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 3 FOR REVISION				



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
mm .X $\pm .25$.XX $\pm .13$.XXX $\pm .10$			Angles $\pm 2^\circ$			
DRAWN	WX	5/28/21	TITLE		10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT DIP TYPE, PRESS FIT, EMI CLIP W/ GASKET, W/ HEAT SINK	
CHECKED	RC	5/28/21	SIZE		X	
APPROVED			PART NO.		XFC-1-CS2-EMI-PF-HSK	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			REV.		-	
REF: S00005C			SCALE: NTS		SHEET 3 OF 3	