


# Data sheet chainflex® CF884



Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant



1. Outer jacket: Pressure extruded PVC mixture
2. Overall shield: Braiding made of tinned copper wires
3. Shield foil: Aluminium clad plastic foil
4. Banding: Plastic foil
5. Drain wire: Stranded conductor consisting of tinned copper wires
6. Core insulation: Mechanically high-quality TPE mixture
7. Conductor: Stranded conductor consisting of bare copper wires
8. Strain relief: Plastic centre element



## Example image

For detailed overview please see design table

## Cable structure

	Conductor	Conductor consisting of bare copper wires (according to DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	According to measuring system specification.
	Core identification	According to measuring system specification. ► Design table
	Element shield	Foil taping of optimised, bending-resistant foil shield. Coverage approx. 100% optical
	Overall shield	Braiding made of tinned copper wires. Coverage approx. 60% optical
	Outer jacket	Low-adhesion PVC mixture, adapted to suit the requirements in e-chains®. <b>Colour:</b> Yellow-green (similar to RAL 6018) <b>Printing:</b> black

„00000 m\*\* igus chainflex M CF884.---① -----② E310776 cЯUus AWM

Style 2560 VW-1 AWM I/II A/B 60°C 30V FT1 CE RoHS-II conform

[www.igus.de](http://www.igus.de)    +++ chainflex cable works +++

\* Length printing: Not calibrated. Only intended as an orientation aid.

① / ② Cable identification according to Part No. (see technical table).

Example: ... chainflex CF884.011 (4x(2x0.34)+4x0.5)C E310776 ...

Example image



# Data sheet chainflex® CF884



Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant

## Dynamic information

	Bend radius	e-chain® linear flexible fixed	minimum 15 x d minimum 12 x d minimum 8 x d
	Temperature	e-chain® linear flexible fixed	+5°C up to +70°C -5°C up to +70°C (following DIN EN 60811-504) -15°C up to +70°C (following DIN EN 50305)
	v max.	unsupported	3m/s
	a max.		20m/s <sup>2</sup>
	Travel distance		Unsupported travels up to 10m, Class 1



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

## Guaranteed service life according to guarantee conditions

Double strokes	1 million	3 million	5 million
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]
+5/+15	17.5	18.5	19.5
+15/+60	15	16	17
+60/+70	17.5	18.5	19.5

Minimum guaranteed service life of the cable under the specified conditions.

The installation of the cable is recommended within the middle temperature range.

## Electrical information

	Nominal voltage	50V 30V (following UL)
	Testing voltage	500V

Example image

igus® chainflex® CF884

# Data sheet chainflex® CF884



Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant

## Properties and approvals



Flame-retardant

According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame



Silicone-free

Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)



PFAS FREE

The design of these products does not contain PTFE



UL-verified

Certificate No. V293650: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“



UL/CSA AWM

See table UL/CSA AWM for details



NFPA

Following NFPA 79-2018, chapter 12.9



REACH

In accordance with regulation (EC) No. 1907/2006 (REACH)



RoHS

Following 2011/65/EC (RoHS-II/RoHS-III)



CE

Following 2014/35/EU



## Properties and approvals

### UL/CSA AWM Details

Part No.	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]	
				UL	UL
CF884.001	1589	2560	30	60	60
CF884.006	1589	2560	30	60	60
CF884.009	1589	2560	30	60	60
CF884.011	1589	2560	30	60	60
CF884.015	1589	2560	30	60	60
CF884.022	1589	2560	30	60	60
CF884.028	1589	2560	30	60	60
CF884.032	1589	2560	30	60	60

Example image

igus® chainflex® CF884

# Data sheet chainflex® CF884




Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant

## Typical lab test setup for this cable series

Test bend radius R	approx. 75 - 225 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s <sup>2</sup>



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



## Typical application areas

- For flexing applications, Class 3
- Especially for unsupported travels, Class 1
- Without influence of oil, Class 1
- No torsion, Class 1
- Preferably indoor applications
- Wood/stone processing, packaging industry, feeding, handling, adjusting devices

Example image



UL US  
LISTED

CUL US

NEC  
NFPA

NFPA

CLPA

DNV

REACH

RoHS

clean-  
room

dry  
clean-  
room  
certified

DESINA

CE

# Data sheet chainflex® CF884



Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant

## Technical tables:

### Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm <sup>2</sup> ]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF884.001	(3x(2x0.14)C+(4x0.14)+(2x0.5))C	8.5	41	91
CF884.006	(3x(2x0.14)C+(4x0.14)+(4x0.22)+(2x0.5))C	9.0	50	101
CF884.009	(4x(2x0.25)+2x0.5)C	8.0	44	91
CF884.011	(4x(2x0.34)+4x0.5)C	9.5	64	117
CF884.015	(4x(2x0.14)+4x0.5)C	8.5	44	92
CF884.022	((2x0.25)+5x0.5)C	8.0	44	79
CF884.028	(2x(2x0.15)+(2x0.38))C	7.5	41	58
CF884.032	(3x(2x0.14)C+(3x0.14)C)C	8.0	28	70

**Note:** The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core x = without earth core



### Electrical information

Conductor nominal cross section [mm <sup>2</sup> ]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Maximum current rating at 30 °C [A]
0.14	138.0	2.5
0.15	138.0	2.5
0.22	89.0	5
0.25	79.0	5
0.34	58.0	7
0.38	54.0	7
0.5	39.0	10

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Example image



# Data sheet chainflex® CF884

Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant



## Design table

Part No.	Core group	Colour code	Core design
CF884.001	3x(2x0.14)C	green/yellow, black/brown, red/orange	
	4x0.14	grey, blue, white-yellow, white-black	
	2x0.5	brown-red, brown-blue	
CF884.006	3x(2x0.14)C	green/yellow, black/brown, red/orange	
	4x0.14	grey, blue, white-yellow, white-black	
	4x0.22	brown-yellow, brown-grey, green-black, green-red	
	2x0.5	brown-red, brown-blue	
CF884.009	(4x(2x0.25)	brown/green, blue/violet, grey/pink, red/black	
	2x0.5)C	white, brown	
CF884.011	4x(2x0.34)	black/brown, red/orange, yellow/green, blue/violet	
	4x0.5	blue-white, black-white, red-white, yellow-white	
CF884.015	4x(2x0.14)	brown/green, yellow/violet, grey/pink, red/black	
	4x0.5	blue, white, brown-green, white-green	
CF884.022	2x0.25	white, brown	
	5x0.5	green, yellow, grey, pink, blue	



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



Example image

# Data sheet chainflex® CF884



Measuring system cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket  
● Shielded ● Flame-retardant

## Design table

Part No.	Core group	Colour code	Core design
CF884.028	2x(2x0.15)	green/yellow, pink/blue	
	2x0.38	red/black	
CF884.032	3x(2x0.14)	green/black, yellow/black, red/black	
	3x0.14	grey/pink/black	



Example image

igus® chainflex® CF884



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



PTFE  
FREE

