



Representative Image

Alternate Catalog No. S201UDC-K5**Catalog No. 2CDS271517R0357****Description: S200UDC MCB 1P K 5A 60VDC BCPD****UPC No 4016779825986****Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

System pro M compact S200UDC current limiting miniature circuit breakers are specially designed for DC applications in the scope of UL489. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (K,Z), configurations (1P,2P) and rated currents (up to 63A). The Short-circuit current rating SCCR acc. UL489 is 14 kA. The S200UDC is suitable for DC voltages up to 125 VDC (2 pole). All MCBs of the product range S200UDC comply with UL489, allowing the use for commercial and industrial applications. .

Descriptors

Category

UL 489 Branch Circuit MCBs

Specifications

Number of Poles	1
Tripping Characteristic	K
Rated Current	5 A
Standards	UL 489
Product Main Type	S200UDC
Rated Voltage (V)	(125 V DC)
Interrupting Rating acc. to UL489	(125 V DC) 14 kA
Power Loss	1.7 W at Rated Operating Conditions per Pole 1.675 W