



Representative Image

Catalog No. 9T11A1002G33

Description: 3A,30kVA,480-208Y,115C,N2,K13,ES,DOE

UPC No 783173902097

Home > Transformers > Dry Type Vented > K-Factor

ABB's K-Factor transformers are designed to withstand the additional heating that accompanies the presence of harmonics in electrical systems. K-Factor transformers are designed not to eliminate harmonics, but to withstand their negative effects. They are available with aluminum or copper windings and in all three temperature rise ratings. K-Factor transformers meet DOE 2016 efficiency standards and are UL Listed and Energy Verified. Qualified to the seismic requirements of IEEE-693-2005 and the IBC-2021 and CBC 2022.

Descriptors

Category	K-Factor
----------	----------

Specifications

TransType	QL
Phase	3
PriVoltage	480
SecVoltage	208Y/120
KVA	30.0 KVA
Coil Material	AL
TempRise	115.0 °C
Frequency	60 Hz
AmbTemp	40.0 °C
EnergyEfficiency	DOE 2016
KFactor	K13
Enclosure Type	NEMA 2
Sound	Std

Classifications

UL	Yes
----	-----