

ECO-RAIL-2 POWER SUPPLY 1-PHASE,

IN: 90-264VAC OUT: 24V/2,5ADC

Art.No.: 85132

Weight: 0.500 kg

Country of origin: CN

Model designation: Eco-Rail-2 2.5-100-240/24

INPUT: 100...240 V AC

OUTPUT: 23...28 V DC


Current: 2.5 A

Mains failure bridging min.

min. 20 ms (115 V AC); min. 100 ms (230 V AC)

Link to Product**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/85132
GTIN	4048879694469
Customs tariff number	85044083
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701

ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85044083
EAN	4048879694469
Packaging unit	1

Electrical data

Parallel connection	No
Series connection	Yes
Number of devices series connection max.	2

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC min.	100 V
Input voltage AC max.	240 V
Nominal input voltage AC	100 V ... 240 V
Nominal current AC	1.3 A @ 100 V, 0.6 A @ 240 V
Inrush current max.	20 A @ 230 V
Efficiency	84 % @ 115 V AC 85 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	4 A

Electrical data | Output

Output voltage adjustable	Yes
Output voltage DC	24 V
Output voltage DC min.	23 V
Output voltage DC max.	28 V
Output current	2,5 A
Spikes (s-s) max.	50 mV
Ripple effective max.	10 mV

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	Yes
Short-circuit protection output	Yes

Mechanical data | Mounting data

Height	125 mm
Width	50 mm
Depth	84 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Electromagnetic compatibility

Interference emission	IEC 61000-3-2
-----------------------	---------------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	40 °C
Derating	40 °C
Ambient temperature (storage, transport)	-20 °C ... 85 °C
Relative humidity (operation)	20 % ... 90 %
Additional condition relative humidity	no condensation

Conformity

Product standard	EN IEC 61010-2-201
------------------	--------------------

Connection type 2

Family construction form	terminal
No. of poles	3
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	PE
PIN 2	N
PIN 3	L
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	-
PIN 2	-
PIN 3	+
PIN 4	+