

Catalog No. HSFR6-1-4

Description: MED WALL SHRINK

UPC No 786210239491

Home > Connectivity & Grounding > Shrink-Kon > Heat shrinkable tube

Heavy-Wall Heat-Shrinkable Tubing - Flame Retardant for Cable Range 6 - 2 AWG, Expanded Diameter 3/4 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

Representative Image

Descriptors

Category	Heat shrinkable tube
Special Features	Insulates and protects electrical splices and terminations.

Specifications

Shrink Ratio	3:1
Voltage Rating	600 V
Flammability	Flame Retardant
Color	Black

Classifications

Brand Name	Shrink-Kon
------------	------------

Dimensions

Length	48 in
--------	-------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	19.05 mm
Inner diameter before heat-shrink	0.75 inch

by ABB

ETIM	EC000217 Shrink tubing
Inner diameter after heat-shrink	6.096 mm
Inner diameter after heat-shrink	0.24 inch
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	2.286 mm
Wall thickness after shrinking	0.09 inch
Length	1.22 m
Length	4 ft
Operation temperature	-55-+110 °C
Operation temperature	-67-+230 °F
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	Y