

## Catalog No. THHQB2170

**Description:** THHQB MCB 70A 22kA 2P 120/240V

**UPC No** 783164135060

**Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 2170 Amps 70 A



Representative Image

### Descriptors

|              |                                   |
|--------------|-----------------------------------|
| Category     | Q-Line Miniature Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On)            |
| GO Schedule  | EB                                |

### Specifications

|                                 |                        |
|---------------------------------|------------------------|
| Trip Style                      | Non-Interchangeable    |
| Frame Type                      | Q-Line                 |
| Amperage                        | 70 A                   |
| System Voltage                  | 120 Vac<br>120/240 Vac |
| Poles                           | 2                      |
| Trip Function                   | LI                     |
| Continuous Current Rated        | Standard               |
| 120 Vac Interrupting Rating     | 22 KAIC                |
| 120/240 Vac Interrupting Rating | 22 KAIC                |
| Suitable for Reverse Feed       | Yes                    |
| Long Time                       | Fixed                  |
| Instantaneous                   | Fixed                  |
| Protective Relays               | No                     |
| Current Metering                | No                     |
| Special Markings                | HACR                   |
| GSA Compliance                  | No                     |

### Classifications

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|