

MET 1-PHASE CONTROL AND ISOLATION TRANSFORMER

P: 4000VA IN: 230VAC+/- 5% OUT: 230VAC

Art.No.: 86110

Weight: 32.000 kg



Country of origin: CZ

Model designation: MET 4000-230+-5%/230

Single-phase - Control and Isolation Transformers

4000 VA

Isolation class T 40/B

Link to Product
Illustration


Product may differ from Image


Commercial data

URL Webshop	https://shop.murrelektronik.com/86110
GTIN	4048879078795
Customs tariff number	85043200
ECLASS-6.0	27031302

ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-7.1	27031302
ECLASS-8.0	27031302
ECLASS-8.1	27031302
ECLASS-9.0	27031302
ECLASS-9.1	27031302
ECLASS-10.0.1	27031302
ECLASS-10.1	27031302
ECLASS-11.0	27031302
ECLASS-11.1	27031302
ECLASS-12.0	27031302
ECLASS-13.0	27031302
ECLASS-14.0	27031302
ETIM-5.0	EC002486
ETIM-6.0	EC002486
ETIM-7.0	EC002486
ETIM-8.0	EC002486
customs tariff number	85043200
EAN	4048879078795
Packaging unit	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC	230 V
Nominal input voltage AC	219 V ... 230 V
Input voltage 3 AC	242 V
Current input AC	18 A
Nominal current AC	219 V @ 230 V
Inrush current at input voltage 2	337 A
Short-circuit current at input voltage 2	807,5 A

Electrical data | Output

Output voltage adjustable	No
Output voltage AC	230 V
Power rating AC max.	4.000 VA

Device protection | Electrical

Insulation test voltage input - output	4 kV
--	------

Mechanical data | Mounting data

Height	206 mm
Width	198 mm
Depth	250 mm
Suitable for mounting type	Long-hole mounting
Mounting dimension a	200 mm
Mounting dimension b	174 mm
Mounting dimension c	9 mm
Diameter bore	9 mm
Length bore	14 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Ambient temperature (storage, transport)	-40 °C ... 80 °C

Conformity

Product standard

EN IEC 61558-1, EN IEC 61558-2-4, IEC 62041 category 0