



Representative Image

Catalog No. TY225-50X

Description: CABLE TIE 50LB 9IN UV BLACK NYLON

UPC No 5414363061397

Home > Wire & Cable Management > Ty-Rap > Cable ties

"Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/IEC 62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 228mm, Width of 4.8mm, Thickness of 1.3mm , Tensile Strength Rating of 220 Newtons, 1000 Pack"

Descriptors

Category	Cable ties
Special Features	The integrally formed polyamide pawl combines low insertion and high locking strength. The low profile head significantly reduces the potential for snagging during installation. Quick and easy pull through increases productivity, reduces operator fatigue. Tail with finger grip design that helps operator grasp and pull ties snugly. Sure grip tab keeps the tail from popping out while being treated, then holds it it securely for final tightening by hand or tool

Specifications

Material	Nylon/Polyamide 6.6 UV Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	222 newtons , 50 pounds

Classifications

Brand Name	Catamount
Standard	UL E49405 UL E49405

Dimensions

Width	4.7mm , 0.185 in
Length	366 mm , 14.409 in
Thickness	1.2 mm , 0.047 in
Bundle Diameter	3.17 to 102 mm , 0.125 to 4.016 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant