

## Catalog No. TY28MX-A

**Description:** CABLE TIE 50LB 14IN



Representative Image

**UPC No 786209999085**

**Home > Wire & Cable Management > Ty-Rap > Cable ties**

Cable Tie, Heat Stabilized, Ultraviolet Resistant Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F) for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 21S Rated, Length of 360.68mm (14.2 Inches), Width of 4.8mm (0.19 Inch), Thickness of 1.27mm (0.05 Inch), Tensile Strength Rating of 222 Newtons (50 pounds), Bulk Pack

### Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

### Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	49.9 pounds , 222 newtons

### Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

### Dimensions

Width	0.19 in , 4.7 mm
Length	14.2 in , 360 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.31 to 3.74 in , 8 to 95 mm

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

ETIM	EC000046 Cable tie
Band width	4.7 mm
Length belt/tape/tie	360 mm
Length belt/tape/tie	14.2 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	95 mm
Min. holding force	222 N
Model	Internal toothed
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y