



300 °C Series



Platinum temperature sensor with wires

For medium temperatures




Benefits & characteristics

- Excellent long-term stability
- Low self-heating
- Fast response time
- Optimal price/performance ratio
- Metallized backside available
- Au-coated Ni-wire available
- Perpendicular wires available
- Customer-specific sensors available upon request



Illustration ¹⁾



¹⁾ for actual size see dimensions in order information

H = Substrate Height

H2 = Height

W = Width

L = Length

L_w = Wire length

Dimension tolerances:

W ±0.2 mm, L ±0.2 mm, H ±0.1 mm, H2 ±0.3 mm,

L_w (up to 30 mm) ±1 mm



Technical data

Operating temperature range:	-200 °C to +300 °C	
Nominal resistance:*	100 Ω at 0 °C	
	500 Ω at 0 °C	
	1000 Ω at 0 °C	
	2000 Ω at 0 °C	
	5000 Ω at 0 °C	
	10'000 Ω at 0 °C	
Characteristics curve:*	3850 ppm/K	
Long-term stability:	< 0.04 % at 1000 h at maximal operating temperature	
Tolerance class: * (dependent on temperature range)		iST reference
	IEC 60751 F0.15	A
	IEC 60751 F0.3	B
	IEC 60751 F0.6	C
	IEC 60751 F0.1	Y
Connection:*	Ni-wire Au-coated, Ø 0.2 mm	
	Ni-flat-wire Au-coated, 0.2 x 0.4 mm (HxW) (solderable, weldable, crimpable)	
	Ag-wire, Ø 0.25 mm	
	Ni-wire, Ø 0.2 mm	
Alternative wire construction: *	Inverted wires	
	Perpendicular wires	
Recommended applied current: ¹⁾ ¹⁾Self-heating must be considered	1 mA at 100 Ω	
	0.5 mA at 500 Ω	
	0.3 mA at 1000 Ω	
	0.2 mA at 2000 Ω	
	0.14 mA at 5000 Ω	
	0.1 mA at 10'000 Ω	
Design:	ESD-optimized ²⁾	
Other alternatives:*	- Metallized backside - Housed in round ceramics (for dry environments only) - Grouped and paired - Substrate thickness - Wire length	

* Customer-specific alternatives available



Order Information

Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
3W Ni-wire Au coated, Ø 0.2 mm							
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.161.3K.Y.020	7	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.15 (class A)	On request	P1K0.161.3K.A.020	7	
1000 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	On request	P1K0.161.3K.B.020	7	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.202.3W.Y.010	10	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	155548	P0K1.202.3W.A.010	10	²⁾ ESD optimized
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	155549	P0K1.202.3W.B.010	10	²⁾ ESD optimized
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.202.3K.Y.015	15	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101250	P0K1.202.3K.A.015	15	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101243	P0K1.202.3K.B.015	15	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K5.202.3K.Y.015	15	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101173	P0K5.202.3K.A.015	15	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101174	P0K5.202.3K.B.015	15	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	156194	P1K0.202.3W.Y.010	10	²⁾ ESD optimized
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	155750	P1K0.202.3W.A.010	10	²⁾ ESD optimized
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	155528	P1K0.202.3W.B.010	10	²⁾ ESD optimized
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101209	P0K1.216.3K.Y.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.15 (class A)	101210	P0K1.216.3K.A.010	10	
100 Ω	216	2.5 x 1.6 x 0.65 / 1.3	F0.3 (class B)	101211	P0K1.216.3K.B.010	10	
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	On request	P0K1.308.3K.Y.007	7	Wire Ø 0.15 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	101941	P0K1.308.3K.A.007	7	Wire Ø 0.15 mm
100 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	101942	P0K1.308.3K.B.007	7	Wire Ø 0.15 mm
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.520.3K.Y.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101239	P0K1.520.3K.A.010	10	
100 Ω	520	5.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101240	P0K1.520.3K.B.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.102.3K.Y.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101242	P0K1.102.3K.A.010	10	
100 Ω	102	10.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101241	P0K1.102.3K.B.010	10	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ±0.2, W ±0.2, H ±0.1, H2 ±0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

3FW Ni flat wire Au-coated, 0.2 x 0.4 mm (HxW)

100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155742	P0K1.202.3FW.Y.007	7	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155761	P0K1.202.3FW.A.007	7	²⁾ ESD optimized
100 Ω	202	1.8 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155743	P0K1.202.3FW.B.007	7	²⁾ ESD optimized
100 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P0K1.202.3FW.Y.010	10	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.15 (class A)	101084	P0K1.202.3FW.A.010	10	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100997	P0K1.202.3FW.B.010	10	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P0K5.202.3FW.Y.007	7	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.15 (class A)	101040	P0K5.202.3FW.A.007	7	
500 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.3 (class B)	100990	P0K5.202.3FW.B.007	7	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	155752	P1K0.202.3FW.Y.007	7	²⁾ ESD optimized
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.15 (class A)	155751	P1K0.202.3FW.A.007	7	²⁾ ESD optimized
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.3 (class B)	155041	P1K0.202.3FW.B.007	7	²⁾ ESD optimized
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.1 (class Y)	On request	P1K0.202.3FW.Y.010	7	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.15 (class A)	101577	P1K0.202.3FW.A.010	7	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.1	F0.3 (class B)	101007	P1K0.202.3FW.B.010	7	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100593	P0K1.232.3FW.Y.007	7	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100631	P0K1.232.3FW.A.007	7	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100592	P0K1.232.3FW.B.007	7	
500 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100714	P0K5.232.3FW.Y.007	7	
500 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100715	P0K5.232.3FW.A.007	7	
500 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100716	P0K5.232.3FW.B.007	7	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	100595	P1K0.232.3FW.Y.007	7	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	100786	P1K0.232.3FW.A.007	7	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100594	P1K0.232.3FW.B.007	7	
2000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100924	P2K0.232.3FW.B.007	7	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L $\pm$ 0.2, W $\pm$ 0.2, H $\pm$ 0.1, H2 $\pm$ 0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
----------------------------	------	---	--------	------------	------------------------------------	-------------------	---------

3FW Ni flat wire Au-coated, 0.2 x 0.3 mm (HxW)

1000 Ω	216	2.0 x 1.6 x 0.65 / 1.3	F0.1 (class Y)	101169	P1K0.216.3FW.Y.007	7	
1000 Ω	216	2.0 x 1.6 x 0.65 / 1.3	F0.15 (class A)	101018	P1K0.216.3FW.A.007	7	
1000 Ω	216	2.0 x 1.6 x 0.65 / 1.3	F0.3 (class B)	100847	P1K0.216.3FW.B.007	7	

3FW Ni flat wire Au-coated, 0.2 x 0.4 mm, on thin substrate (thickness 0.4 mm)

5000 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.3 (class B)	101290	P5K0.520.3FW.B.007.D	7	
10000 Ω	520	5.0 x 2.0 x 0.4 / 1.05	F0.3 (class B)	100718	P10K.520.3FW.B.010.D	10	

3FK Ni flat wire Au-coated, one lead on each side of the element

1000 Ω	212	2.0 x 1.2 x 0.25 / 0.6	F0.3 (class B)	104190	P1K0.212.3FK.B.007.T.S	7	axial
---------------	-----	------------------------	----------------	--------	------------------------	---	-------

3SK Ag wire, Ø 0.25 mm, perpendicular wire, metallized backside

100 Ω	161	1.6 x 1.2 x 0.25 / 0.85	F0.1 (class Y)	On request	P0K1.161.3SK.Y.010.M	10	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.85	F0.15 (class A)	100623	P0K1.161.3SK.A.010.M	10	
100 Ω	161	1.6 x 1.2 x 0.25 / 0.6	F0.3 (class B)	100627	P0K1.161.3SK.B.010.M	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P0K1.232.3SK.Y.010.M	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P0K1.232.3SK.Y.010.M	10	
100 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100509	P0K1.232.3SK.B.010.M	10	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.232.3SK.Y.015.M	15	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.15 (class A)	On request	P1K0.232.3SK.A.015.M	15	
1000 Ω	232	2.3 x 2.0 x 0.65 / 1.3	F0.3 (class B)	100457	P1K0.232.3SK.B.015.M	15	

3W Ni wire, Ø 0.2 mm

100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101104	P0K1.202.3W.A.010	10	
100 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101101	P0K1.202.3W.B.010	10	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.1 (class Y)	On request	P1K0.202.3W.Y.007	7	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.15 (class A)	101088	P1K0.202.3W.A.007	7	
1000 Ω	202	2.0 x 2.0 x 0.65 / 1.3	F0.3 (class B)	101038	P1K0.202.3W.B.007	7	



Nominal Resistance at 0 °C	Size	Dimensions (L x W x H / H2 in mm) L ± 0.2 , W ± 0.2 , H ± 0.1 , H2 ± 0.3 mm	Class*	Order code	Product name (secondary reference)	Wire length in mm	Special
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.1 (class Y)	On request	P1K0.308.3W.Y.025	25	Wire $\varnothing$ 0.15 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.15 (class A)	104055	P1K0.308.3W.A.025	25	Wire $\varnothing$ 0.15 mm
1000 Ω	308	3.0 x 0.8 x 0.25 / 0.6	F0.3 (class B)	104059	P1K0.308.3W.B.025	25	Wire $\varnothing$ 0.15 mm

*Alternative class for each product is available upon request

Additional documents

Application note

Document name:

ATP_E



Order Information

Platinum Sensor - Secondary reference

Material

P = Platinum

TCR

= Pt 3850 ppm/K G = Pt 3911 ppm/K
U = Pt 3750 ppm/K W = Pt 3850 ppm/K (extended operating temperature range in class A)

Resistance in Ω at 0°C

Size in mm

Operating temperature range

1 = -50 °C to + 150 °C	6 = -200 °C to + 600 °C
2 = -50 °C to + 200 °C	7 = -200 °C to + 750 °C
3 = -200 °C to + 300 °C	8 = -200 °C to + 850 °C
4 = -200 °C to + 400 °C	10 = -70 °C to + 1000 °C

Connections

S = SIL	FK = Flat wire customer specific
I = Insulated wire	SW = Perpendicular wire
K = Extended wire	L = Insulated stranded wire
W = Wire	E = Enameled Cu-wire
FW = Flat wire	SE = Perpendicular enameled Cu-wire

Tolerance class

A = IEC 60751 F0.15	K = Customer-specific
B = IEC 60751 F0.3	P = Pair
C = IEC 60751 F0.6	G = Group
Y = IEC 60751 F0.1	

Wire length in mm

Special

T = Substrate thickness 0.25 mm	M = Metallized backside
D = Substrate thickness 0.38 mm	U = Inverted welding
R = Round housing	S = Special
W = Sintered powder	

P 0K1. 232. 3 FW. B. 010. U



Innovative Sensor Technology IST AG • Stegrütistrasse 14 • 9642 Ebnat-Kappel • Switzerland
+41 71 992 01 00 • info@ist-ag.com • www.ist-ag.com

Technical specifications are subject to change without prior notice. The information contained in this data sheet has been carefully reviewed and is believed to be accurate; however, no liability is assumed for any errors or omissions. Continuous exposure to extreme operating conditions may impact product lifetime or reliability. The customer is solely responsible for assessing the suitability and fitness of the product for their specific application. This product is not designed, authorized, or warranted for use in life support or safety-critical applications. The customer agrees to hold the supplier harmless from any claims, damages, or liabilities arising from such use. No explicit or implied warranties, including but not limited to warranties of merchantability or fitness for a particular purpose, are provided. The material provided herein may not be reproduced, adapted, merged, translated, stored, or utilized in any form without prior written consent from the copyright holder. No transfer of any intellectual property rights is granted or implied. All rights reserved.