



Representative Image

Alternate Catalog No. AF38B-30-00RT-14

Catalog No. 1SBL297060R1400

Description: AF38B-30-00RT-14 250-500V50/60HZ-DC Contactor

UPC No 3471523126749

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF38B..RT 3-pole contactors comply with the latest railway rolling stock standards and allow installation in passengers or driver cabins for trains frequently operating tunnels or undergrounds. They are mainly used for controlling 3-phase motors and power circuits up to 690 V AC and 220 V DC. Improve the compactness of the installations thanks to reduced dimension and side-by-side mounting requiring less 15% width (without spacing) from -40 °C up to +70 °C. Meet all main rolling stocks standards: IEC 60947-4-1, IEC 60947-5-1, IEC 60077-1-2 and applicable parts of EN 50155 standards, shocks and vibration withstand conforming to IEC 61373 cat. 1, class B. Reach the highest levels in fire and smoke behaviour with compliance to European standard EN 45545-2 (HL2, HL3 hazard levels) in group mounting. Reduce train energy with lighter devices and requiring 68% less coil energy consumption in operation. Electronic coil interface accepting sinusoidal AC 50/60 Hz control supplies included inside Ucmin.... Ucmax voltage range. Max permitted AC 50/60 Hz control voltage must not be exceeded (see technical data). Wide range of auxiliary contact blocks for front and side mounting.

Descriptors

Category	AF Contactors
Block Contactor Type	3-Pole Contactor

Specifications

Product Type	AF
General Use Rating UL/CSA	(600 V AC) 50 A
Object Classification Code	Q
Terminal Type	Ring-Tongue Terminals
Rated Control Circuit Voltage	50 Hz /60 Hz DC Operation 250 ... 500 V
Number of Main Contacts NO	3
Number of Main Contacts NC	0
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Number of Auxiliary Contacts NO	0
RoHS Status	Following EU Directive 2011/65/EU
Rated Operational Voltage	Main Circuit 690 V
Number of Auxiliary Contacts NC	0
Rated Operational Current AC-1	(690 V) 40 °C 50 A
Horsepower Rating UL/CSA	(220 ... 240 V AC) Three Phase 10 hp (440 ... 480 V AC) Three Phase 20 hp (550 ... 600 V AC) Three Phase 25 hp (120 V AC) Single Phase 2 hp (200 ... 208 V AC) Three Phase 10 hp (240 V AC) Single Phase 5 hp
Rated Frequency	Main Circuit 50Hz Main Circuit 60 Hz
Rated Operational Current AC-3	(380 / 400 V) 60 °C 38 A
Operate Time	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
Screw Terminal Type	Ring-Tongue Terminals

by ABB

Classifications

ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 5.0	EC000066 - Magnet contactor, AC-switching

Dimensions

Product Net Weight	0.36 kg
Product Net Depth / Length	86 mm
Product Net Width	45 mm
Product Net Height	86 mm

Package Information

Package Level 1 Width	87 mm
Package Level 1 Height	47 mm
Package Level 1 Depth / Length	87 mm
Package Level 1 EAN	3471523126749
Package Level 1 Units	box 1 piece
Package Level 2 Width	250 mm
Package Level 2 Height	315 mm
Package Level 1 Gross Weight	0.36 kg
Package Level 2 Units	21 piece
Package Level 3 Units	1080 piece
Package Level 2 Depth / Length	300 mm
Package Level 2 Gross Weight	16.2 kg

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85364900