

Steel City Pre-Ganged boxes

Accessories and covers



3G 1/2 3/4CN



SGP



2 GC



| Cat. No. | Volume (Cu. in.) | Number of Gangs | Width (in.) | Knockouts | | Accepts |
|---|------------------|-----------------|-------------|----------------|----------------|--------------|
| | | | | sides | bottom | |
| Pre-ganged boxes – 1 5/8 in. deep x 4 1/2 in. high | | | | | | |
| 2G 1/2 3/4CN | 45.0 | 2 | 6 13/16 | 4x 1/2; 4x 3/4 | 3x 1/2; 2x 3/4 | 2 GC or 3 GC |
| 3G 1/2 3/4CN | 58.0 | 3 | 8 5/8 | 6x 1/2; 4x 3/4 | 6x 1/2; 4x 3/4 | 3 GC or 4 GC |
| 4G 1/2 & 3/4-CN | 70.0 | 4 | 10 7/16 | 6x 1/2; 6x 3/4 | 6x 1/2; 4x 3/4 | 4 GC or 5 GC |
| 5G 1/2 3/4CN | 85.0 | 5 | 12 1/4 | 8x 1/2; 6x 3/4 | 6x 1/2; 4x 3/4 | 5 GC or 6 GC |
| 6G 1/2 3/4CN | 98.0 | 6 | 14 1/16 | 8x 1/2; 8x 3/4 | 6x 1/2; 4x 3/4 | 6 GC |

3G 1/2 3/4CN or 4G 1/2 & 3/4-CN, all CIGBC covers have tapped holes spaced to accommodate standard switches and receptacles. Lateral spacing 1 13/16 in.



| Cat. No. | Volume (Cu. in.) | Number of Gangs | Width (in.) | Accepts |
|---|------------------|-----------------|-------------|---------------------------------|
| 3/4 in. raised covers – 4 13/16 in. high | | | | |
| 2 GC | 8.5 | 2 | 7 | 2G 1/2 3/4CN |
| 3 GC | 13.5 | 3 | 8 25/32 | 2G 1/2 3/4CN or 3G 1/2 3/4CN |
| 4 GC | 18.3 | 4 | 10 5/8 | 3G 1/2 3/4CN or 4G 1/2 & 3/4-CN |
| 5 GC | 23.0 | 5 | 12 7/16 | 4G 1/2 & 3/4-CN or 5G 1/2 3/4CN |
| 6 GC | 28.3 | 6 | 14 1/4 | 5G 1/2 3/4CN or 6G 1/2 3/4CN |

| Cat. No. | Adjustment (in.) | Number of Gangs | Width (in.) | Accepts |
|----------------------------------|------------------|-----------------|-------------|------------------------------|
| Raised cover - adjustable | | | | |
| 52CADJ3612 | 3/4 - 1 1/2 | 3 | 8 7/8 | 2G 1/2 3/4CN or 3G 1/2 3/4CN |

| Cat. No. | Description |
|---------------------------------------|--|
| Low voltage partitions (steel) | |
| SGP | Steel low voltage partition for use with Steel City Pre-Ganged boxes, when conductors are connected to different sources |

In accordance with C.E.C. 2012 Edition, Rule 12-3030: Conductors that are connected to different power or distribution transformers or other different sources of voltage shall not be installed in the same box, cabinet, or fitting unless a barrier of sheet steel not less than 1.3 mm thick or a flame-retardant nonmetallic insulating material not less than 1.6 mm in thickness is used to divide the space into separate compartments for the conductors of each system.