

Product data sheet

Characteristics

9007AB22

Snap limit switch, 9007, 600 VAC 15amp ab
+options



Main

Range of Product	9007
Series name	Heavy duty
Product or Component	Snap limit switch
Type	
Device short name	9007AO/CO
Body type	Fixed

Complementary

Mounting Mode	-
Operator profile	Plunger head
Material	Metal
Body Material	Cast zinc
Operator material	Cast zinc
Fixing Mode	By the body
Movement of operating head	Linear
Type of operator	Spring return roller lever plunger metal LH bracket + 0.22" roller
Switch actuation	By 30° cam
Type of approach	Traverse approach, 2 directions
Electrical connection	1...2 6 binder head screw terminals AWG 22...AWG 14)
Number of poles	1
Contacts type and composition	NC-NO SPDT-DB
Contact form	Form Z
Contact operation	Snap action
Number of steps	1
Contacts material	Silver contacts
Positive opening	Without
Terminals description ISO n°1	(1-2)NC (3-4)NO
Minimum force for tripping	0.5 lbf
Maximum force for tripping	0.5 lbf
[Ie] rated operational current	5 A 600 V AC, A600 NEMA rating designation 6 A 480 V AC, A600 NEMA rating designation 10 A 240 V AC, A600 NEMA rating designation 15 A 120 V AC, A600 NEMA rating designation 0.02 A 600 V DC 0.2 A 250 V DC 0.5 A 125 V DC
[Ithe] conventional enclosed thermal current	15 A
[Ui] rated insulation voltage	600 V 3)UL 508 contact block 600 VCSA C22.2 No 14 contact block
Width	0.95 in (24.13 mm)
Height	2.5 in (63.50 mm)
Depth	2.44 in (61.98 mm)
Net Weight	0.17 lb(US) (0.08 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

NEMA degree of protection	NEMA 1 Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)

Ordering and shipping details

Category	21491-9007 A SNAP SWITCHES
Discount Schedule	DS1
GTIN	785901722724
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	1.70 in (4.318 cm)
Package 1 Length	2.50 in (6.35 cm)
Package 1 Weight	2.40 oz (68.04 g)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.61 lb(US) (3.905 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------