

Product data sheet

Characteristics

9007CA1

limit switch lever arm, 9007C, 2 inch long cast zinc lever arm, 0.625 inch diameter roller, 0.25 inch wide roller



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch lever
Device short name	9007C
Associated head	9007T5 9007C 9007N 9007T10 9007B 9007A
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 2 in (50.80 mm) --
Type of roller	1 steel outside roller 0.63 in (16.00 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21493-9007 ARMS FOR AW,C
Discount Schedule	DS1
GTIN	785901794325
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.60 in (1.524 cm)
Package 1 Width	0.90 in (2.286 cm)
Package 1 Length	2.70 in (6.858 cm)
Package 1 Weight	1.60 oz (45.359 g)
Unit Type of Package 2	S01
Number of Units in Package 2	50
Package 2 Height	5.91 in (15.0 cm)

Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.44 lb(US) (2.468 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------