

Features



- Rugged, cost-effective, and easy-to-install multi-segment indicators
- Illuminated segments provide easy-to-see operator guidance and indication of equipment status
- Up to five stacked colors available
- Available in black or light gray housing
- Audible models available with standard, sealed, or omni-directional audible element
- Compact devices are completely self-contained - no controller needed
- 12 V DC to 30 V DC operation with IO-Link control
- No assembly required


Models

Color/Function Position												
Housing	C1	F1	C2	F2	C3	F3	C4	F4	C5	F5	C6*	
TL50BL	G	2	R		Y	1						
Blank = ON Solid						Blank = No Audible						
G = Green Y = Yellow R = Red B = Blue W = White						A = Audible						
1 = Rotating						ALS = Sealed Audible Continuous Tone ALS3 = Sealed Audible Pulsed Tone ALS4 = Sealed Audible Staccato Tone AOS = Omni-Directional Sealed Audible Continuous Tone AOSI = Omni-Directional Sealed Audible Continuous Tone with Intensity Adjust AOS3 = Omni-Directional Sealed Audible Pulsed Tone AOS3I = Omni-Directional Sealed Audible Pulsed Tone with Intensity Adjust AOS4 = Omni-Directional Sealed Audible Staccato Tone AOS4I = Omni-Directional Sealed Audible Staccato Tone with Intensity Adjust						
Color/Function notes: C1-C5 are available as color or audible segments *C6 is only available as an audible segment						K = IO-Link						
Blank = Black C = Gray						Blank = Black						
Q = Integral 4-pin M12 male quick-disconnect connector QP = 150 mm (5.9) cable with 5-pin M12 male quick-disconnect connector						Q						

Example models include: TL50BLWBGYRKQ or TL50BLGYRALSQK.

The first color listed is the bottom color, going up in successive order.

Wiring



IO-Link Process In Data

IO-Link® is a point-to-point communication link between a master device and a sensor and/or light. It can be used to automatically parameterize sensors or lights and to transmit process data. For the latest IO-LINK protocol and specifications, please visit www.io-link.com.

Process Data is transmitted cyclically to the IO-Link device from the IO-Link master. These parameters are written to the TL50BL acyclically and are used to perform one of the following functions:

- Tower light turns off
- Tower light turns on or rotates (designated by model)
- Tower light flashes

IO-Link Process Data Out for the TL50BL

Subindex	Name	Light Segment	Audible Segment
1	Segment 1	Off/On/Flash	Off/On
2	Segment 2	Off/On/Flash	Off/On
3	Segment 3	Off/On/Flash	Off/On
4	Segment 4	Off/On/Flash	Off/On

Continued on page 2



Continued from page 1

IO-Link Process Data Out for the TL50BL

Subindex	Name	Light Segment	Audible Segment
5	Segment 5	Off/On/Flash	Off/On
6	Segment 6	N/A	Off/On

Specifications

Supply Voltage and Current

12 V DC to 30 V DC
Maximum current per LED color:150 mA at 12 V DC
80 mA at 24 V DC
70 mA at 30 V DC

Maximum current for Standard Audible Alarm: 50 mA

Maximum current for Omni-Directional Sealed Audible: 70 mA

Maximum current for Sealed Audible Alarm: 60 mA

Supply Protection Circuitry

Protected against reverse polarity and transient voltages

Audible Adjustment

Standard Audible Alarm: Unscrew the cover (up to 1.5 turns maximum) to adjust the audible intensity. (Do not exceed 1.5 turns or the cover may detach during operation.) For maximum intensity, rotate the center plug 180° counterclockwise to remove it.**Sealed Audible Alarm and Omni-Directional Sealed Audible Alarm with Intensity Adjustment:** Rotate the front cover until the desired intensity is reached.**Omni-Directional Sealed Audible Alarm:** No adjustment.

Audible Alarm

Standard Audible Alarm: 2.7 kHz ± 500 Hz oscillation frequency; maximum intensity 92 dB at 1 m (3.3 ft) (typical)**Sealed Audible Alarm:** 2.9 kHz ± 250 Hz oscillation frequency; maximum intensity 94 dB at 1 m (3.3 ft) (typical)**Omni-Directional Sealed Audible Alarm:** 2.1 kHz ± 250 Hz oscillation frequency; maximum intensity 99 dB at 1 m (3.3 ft) (typical)**Omni-Directional Sealed Audible Alarm with Intensity Adjustment:** 2.1 kHz ± 250 Hz oscillation frequency; maximum intensity 95 dB at 1 m (3.3 ft) (typical)**Typical Reduction in Sound Intensity with Audible Adjustment (maximum to minimum)**

- **Standard Audible:** 30 dB
- **Sealed Audible:** 20 dB
- **Omni-Directional Sealed Audible:** 12 dB

Dimensions

All measurements are listed in millimeters [inches], unless noted otherwise. The measurements provided are subject to change.

Dimensions	# of Colors	Tower Height (H)			
		Non-Audible	Standard Audible ⁽¹⁾	Sealed Audible	Omni-Directional Sealed Audible
	1	46.2 mm (1.8 in)	77.1 mm (3.1 in)	100.2 mm (4 in)	114.2 mm (4.5 in)
	2	72 mm (2.8 in)	102.9 mm (4.1 in)	126 mm (5 in)	140 mm (5.5 in)
	3	97.8 mm (3.8 in)	128.7 mm (5.1 in)	141.8 mm (6 in)	165.8 mm (6.5 in)
	4	123.6 mm (4.8 in)	154.5 mm (6.1 in)	177.6 mm (7 in)	191.6 mm (7.5 in)
	5	149.4 mm (5.8 in)	180.5 mm (7.1 in)	203.4 mm (8 in)	217.4 mm (8.5 in)
	6	-	206.1 mm (8.1 in)	229.2 mm (9 in)	243.2 mm (9.5 in)

⁽¹⁾ Tower height (H) with top unscrewed approximately 3.5 mm (0.18 in) to allow sound to escape

Required Overcurrent Protection

**WARNING:** Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table. Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply. Supply wiring leads < 24 AWG shall not be spliced. For additional product support, go to www.bannerengineering.com.





Supply Wiring (AWG)	Required Overcurrent Protection (A)	Supply Wiring (AWG)	Required Overcurrent Protection (A)
20	5.0	26	1.0
22	3.0	28	0.8
24	1.0	30	0.5

Certifications

Banner Engineering BV
Park Lane, Culliganlaan 2F bus 3
1831 Diegem, BELGIUM

Accessories

Cordsets


4-Pin Double-Ended M12 Female to M12 Male Cordsets					
Model	Length	Style	Dimensions		Pinout
MQDEC-401SS	0.31 m (1 ft)	Male Straight/Female Straight			Female
MQDEC-403SS	0.91 m (2.99 ft)				1 = Brown 2 = White 3 = Blue 4 = Black
MQDEC-406SS	1.83 m (6 ft)				Male
MQDEC-412SS	3.66 m (12 ft)				1 = Brown 2 = White 3 = Blue 4 = Black
MQDEC-415SS	4.58 m (15 ft)				Female
MQDEC-420SS	6.10 m (20 ft)				1 = Brown 2 = White 3 = Blue 4 = Black
MQDEC-430SS	9.14 m (30.2 ft)				Male
MQDEC-450SS	15.2 m (49.9 ft)				1 = Brown 2 = White 3 = Blue 4 = Black

Mounting Brackets





All measurements are listed in millimeters [inches], unless noted otherwise. The measurements provided are subject to change.

SMB30A <ul style="list-style-type: none"> Right-angle bracket with curved slot for versatile orientation Clearance for M6 ($\frac{1}{4}$ in) hardware Mounting hole for 30 mm sensor 12-gauge stainless steel <p>Hole center spacing: A to B=40 Hole size: A=\varnothing 6.3, B= 27.1×6.3, C=\varnothing 30.5</p>	
--	---

<p>SMB30FA</p> <ul style="list-style-type: none"> • Swivel bracket with tilt and pan movement for precise adjustment • Mounting hole for 30 mm sensor • 12-gauge 304 stainless steel • Easy sensor mounting to extrude rail T-slot • Metric- and inch-size bolt available <p>Bolt thread: SMB30FA, A= 3/8 - 16 × 2 in; SMB30FAM10, A= M10 - 1.5 × 50 Hole size: B= \varnothing 30.1</p>	
---	---

SMB30MM	
	<ul style="list-style-type: none">• 12-gauge stainless steel bracket with curved mounting slots for versatile orientation
	<ul style="list-style-type: none">• Clearance for M6 (1/4 in) hardware
	<ul style="list-style-type: none">• Mounting hole for 30 mm sensor
Hole center spacing:	A = 51, A to B = 25.4
Hole size:	A = 42.6 × 7, B = ø 6.4, C = ø 30.1

<p>SMBAMS30P</p> <ul style="list-style-type: none"> • Flat SMBAMS series bracket • 30 mm hole for mounting sensors • Articulation slots for 90°+ rotation • 12-gauge 300 series stainless steel <p>Hole center spacing: A=26.0, A to B=13.0 Hole size: A=26.8 x 7.0, B=Ø 6.5, C=Ø 31.0</p>	
--	---

<p>SMBAMS30RA</p> <ul style="list-style-type: none"> Right-angle SMBAMS series bracket 30 mm hole for mounting sensors Articulation slots for 90°+ rotation 12-gauge (2.6 mm) cold-rolled steel <p>Hole center spacing: A=26.0, A to B=13.0 Hole size: A=26.8 x 7.0, B=Ø 6.5, C=Ø 31.0</p>	
<p>SMB30SC</p> <ul style="list-style-type: none"> Swivel bracket with 30 mm mounting hole for sensor Black reinforced thermoplastic polyester Stainless steel mounting and swivel locking hardware included <p>Hole center spacing: A=Ø 50.8 Hole size: A=Ø 7.0, B=Ø 30.0</p>	
<p>LMBE12RA35</p> <ul style="list-style-type: none"> Direct mounting of stand-off pipe, with common bracket type Zinc-plated steel 1/2-14 NPSM nut Mounting distance from the wall to the center of the 1/2-14 NPSM nut is 35 mm <p>Hole center spacing: 20.0</p>	
<p>LMBE12RA45</p> <ul style="list-style-type: none"> Direct mounting of stand-off pipe, with common bracket type Zinc-plated steel 1/2-14 NPSM nut Mounting distance from the wall to the center of the 1/2-14 NPSM nut is 45 mm <p>Hole center spacing: 35.0</p>	

LMB Sealed Right-Angle Bracket

Model	Description	
LMB30RA - Black polycarbonate LMB30RAC - Gray polycarbonate	<ul style="list-style-type: none"> Direct-Mount Models Bracket kit with base, 30 mm adapter, set screw, fasteners, O-rings, and gaskets. 	
LMBE12RA - Black polycarbonate LMBE12RAC - Gray polycarbonate	<ul style="list-style-type: none"> Pipe-Mount Models Bracket kit with base, 1/2-14 pipe adapter, set screw, fasteners, O-rings, and gaskets For use with stand-off pipe (listed and sold separately) 	

Elevated Mount System



Model	Description	Components
SA-M30TE12 - Black Acetal		
SA-M30TE12C - White UHMW	<ul style="list-style-type: none"> Streamlined black acetal or white UHMW stand-off pipe adapter/cover Connects between 30 mm light base and 1/2 in. NPSM/ DN15 pipe Mounting hardware included 	

Continued on page 5

Continued from page 4

Model			Description	Components
Polished 304 Stainless Steel	Black Anodized Aluminum	Clear Anodized Aluminum		
SOP-E12-150SS 150 mm (6 in) long	SOP-E12-150A 150 mm (6 in) long	SOP-E12-150AC 150 mm (6 in) long	<ul style="list-style-type: none"> Elevated-use stand-off pipe (1/2 in. NPSM/DN15) Polished 304 stainless steel, black anodized aluminum, or clear anodized aluminum surface 1/2 in. NPT thread at both ends: one end screws into the internal threads of the light's base, and one end screws into the mounting base adapter/cover Compatible with most industrial environments 	
SOP-E12-300SS 300 mm (12 in) long	SOP-E12-300A 300 mm (12 in) long	SOP-E12-300AC 300 mm (12 in) long		
SOP-E12-900SS 900 mm (36 in) long	SOP-E12-900A 900 mm (36 in) long	SOP-E12-900AC 900 mm (36 in) long		
SA-E12M30 - Black Acetal			<ul style="list-style-type: none"> Streamlined black acetal or white UHMW mounting base adapter/cover Connects between 1/2 in. NPSM/DN15 pipe and 30 mm (1-3/16 in) drilled hole Mounting hardware included 	
SA-E12M30C - White UHMW				

Pipe Mounting Flange

Pipe Mounting Flange				
Model	Description	Construction	Dimensions	
SA-F12	<ul style="list-style-type: none"> Elevated-use stand-off pipes (1/2 in, NPSM/DN15) M5 mounting hardware and nitrile gasket included 	Die-cast zinc base with black paint		
SA-F12-3	<ul style="list-style-type: none"> Elevated-use stand-off pipes (1/2 in, NPSM/DN15) M4 mounting hardware and nitrile blend gasket included 	Black Polycarbonate		

Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. **IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.**

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change. Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to: www.bannerengineering.com.

For patent information, see www.bannerengineering.com/patents.