

120 VAC  
**UL**  
 LISTED  
 7R59  
 Clock Oper. Sw.

### Percentage Timer

#### SPECIFICATIONS


TIME RANGES	15 MIN
TIMING MODE	Continuous ON-OFF
RANGE SETTING	3%-97%, Also 100% ON and OFF Points
SETTING ACCURACY	Within 3% of Full Scale, 10-90%
REPEAT ACCURACY	Within 1% of Full Scale
OUTPUT	SPST, 20A, 1/2 HP 120 VAC
MOTOR VOLTAGES	120 VAC 50/60 Hz (50 Hz. Units Will Be 1/6 Slower Than Listed Speeds.)
TERMINATION	Rear Screw Terminals
MOUNTING	Front Panel
TEMPERATURE RATING	32° to 120°F (0° to 50°C)
WEIGHT	1.4 lbs.

#### MODEL NUMBER

MODEL CP-15M-A

\*CONSULT FACTORY FOR OTHER TIME RANGES & VOLTAGES

#### WIRING



- Precise Fool-proof Operating Mechanism
- Eliminates All Engaging Cams and Latches
- Minimal Panel Space Needed

For continuous ON-OFF control of electrical circuits, the CP Series single circuit repeat cycle timer is a continuous cycling control where the ON or circuit closure time is dial adjusted for a percentage of the total time cycle.

**APPLICATIONS:** Control of pumps, blowers, filters, heating equipment, industrial ovens, laboratory equipment and wherever ON or OFF control is desired as a percentage of the primary fixed total time cycle.

#### DIMENSIONS

