

Product data sheet

Characteristics

9007R17

NEMA limit switch, 9007C, rod clamp, adjustable, 0.25 inch key stock



Main

Range of Product	9007
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	9007T/FT
Associated head	9007CS9 9007T5S9 9007NS9 9007AS9 9007T10S9 9007BS9
Associated complete product	9007FT 9007C..S9 9007T
Movement of operating head	Rotary
Type of operator	Cast zinc spring return rod lever without rod - clamp for use with 1/4" key stock (not supplied)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By any moving part
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21494-9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	785901814122
Nbr. of units in pkg.	1
Package weight(Lbs)	2.72 oz (77.11 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.20 in (3.048 cm)
Package 1 width	1.40 in (3.556 cm)
Package 1 Length	2.00 in (5.08 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	50
Package 2 Weight	9.07 lb(US) (4.114 kg)
Package 2 Height	5.91 in (15 cm)

Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------