



**Main**

Range of Product	9007
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	9007T/FT
Associated head	9007AS9 9007T5S9 9007BS9 9007T10S9 9007NS9 9007CS9
Associated complete product	9007C..S9 9007T 9007FT
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller without lever - roller and clamp only (use 9007R16 or 17)
Type of roller	1 steel optional position 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

**Complementary**

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

**Environment**

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

**Ordering and shipping details**

Category	21494-9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	785901814139
Returnability	No
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	1.60 oz (45.359 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------