



Main

Range of Product	L100/300
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	L100/300
Associated complete product	HML300 L300 L100 ML300 HL300 HML100 HL100 ML100
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller lever 5 in (127.00 mm) --
Type of roller	1 steel center roller 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21519-9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	785901096863
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	7.60 in (19.304 cm)
Package 1 Weight	1.60 oz (45.359 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------