


1476A Multi-Conductor - 300V Power-Limited Tray Cable



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG pairs stranded (7x26) bare copper conductors, twisted pairs, individually shielded plus an overall Beldfoil (100% coverage), PVC insulation, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	# Pairs	AWG	Stranding	Conductor Material
	8	18	7x26	BC - Bare Copper
1		22	7x30	BC - Bare Copper

Total Number of Conductors: 17

Insulation**Insulation Material:**

Insulation Material
PVC - Polyvinyl Chloride

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
20

Inner Shield Drain Wire Stranding: 7x28

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.3462

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 15.240 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2

1476A Multi-Conductor - 300V Power-Limited Tray Cable

3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 7
7	Black & White and Numbered 7
8	Black & White and Numbered 8
Communication	Orange

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
Bulk Cable Weight:	330.380 Kg/Km
Max. Recommended Pulling Tension:	2228.550 N
Min. Bend Radius/Minor Axis:	152.400 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Surface Printing:	BELDEN 1476A E34972 8PR18 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
-------------------	--

Electrical Characteristics (Overall)**Nom. Conductor DC Resistance:**

Description	DCR @ 20°C (Ohm/km)
18 AWG	19.2267
22 AWG	48.2307

1476A Multi-Conductor - 300V Power-Limited Tray Cable

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
14.6661

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 33.794 Ohm/km

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.5 Amps per conductor @ 25°C

Notes (Overall)

Notes: Alternate color coding available upon request.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1476A 0061000	1,000 FT	293.000 LB	BLUE, LIGHT	C	8 FSPR #18 + 1 #22 PVC FS PVC
1476A 0105000	5,000 FT	1,300.000 LB	BLACK	C Z	8 FS PR #18 + 1 #22 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 05-17-2015

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).