

Product availability: Non-Stock - Not normally stocked in distribution facility

**Main**

Base plate style	Style A
Device application	Standard foundry switch Universal mill switch
Device short name	FT
Series name	Severe duty

**Complementary**

[I <sub>th</sub> ] conventional free air thermal current	20 A
[U <sub>i</sub> ] rated insulation voltage	600 V
AWG gauge	AWG 22...AWG 12
Body material	Cast zinc
Cable entry	0.5 in NPT conduit entry
Contact code designation	A600 P600
Contact status	Open A for initial position Open A for middle position Open B for middle position
Contacts material	Silver flashed copper
Contact operation	Snap action
Maximum displacement angle	81 °
Positive opening	Without
Switch actuation	CW and CCW
Tilting angle	6 °
Torque value	12 lbf.in
Tripping angle	5 °

**Environment**

Ambient air temperature for operation	-10...185 °F
Electrical shock protection class	Class 0
IP degree of protection	IP65 IP66 IP67
NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CE CSA UL listed
Protective treatment	Corrosion resistant gray paint
Shock resistance	30 gn

## Ordering and shipping details

Category	21497 - 9007 FT,T OILTIGHT AND FOUNDRY
Discount Schedule	DS1
GTIN	00785901179696
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------