

Product data sheet

Characteristics

XZCPB44P14L5

Pre wired connectors XZ, straight female, M12, 12 pins, cable PUR 5 m



Main

Range of product	Telemecanique Cabling components
Accessory / separate part category	Cabling accessory
Accessory / separate part type	Pre-wired connectors
Series name	Application

Complementary

Electrical connection	Straight female connector M12, 12 pins
Cable connector fixing	Screw-on
Collar material	Metal
Status LED	Without
Cable length	16.40 ft (5 m)
Cable outer diameter	0.33 in (8.5 mm)
Cable composition	12 x 0.14 mm ²
Wire insulation material	PUR
[Ue] rated operational voltage	30 V DC
Line Rated Current	1.5 A
Contact resistance	5000 µOhm
Minimum insulating resistance	100 MOhm
Product Weight	1.01 lb(US) (0.46 kg)

Environment

IP degree of protection	IP69K IP68 IP65
Ambient air temperature for operation	-40...176 °F (-40...80 °C) static 23...176 °F (-5...80 °C) flexing
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22484 - XUW VISION SENSORS
Discount Schedule	DS2
GTIN	3389119086035
Nbr. of units in pkg.	1
Package weight(Lbs)	17.14 oz (486 g)
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	10.24 in (26 cm)
Package 1 Length	11.81 in (30 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Weight	6.15 lb(US) (2.79 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes