



Product: [1624P](#) 

Category 5 Cable, 4 Pair, F/UTP, CMP

Product Description

Category 5 Premise Horizontal Cable (100MHz), 4 Pair, 24 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE , Noisy Environments
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White/Blue & Blue, White/Orange & Orange, White/Green & Green, White/Brown & Brown

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Polyester + Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Material Trade Name	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.235 in (5.97 mm)	No

Overall Cable Diameter (Nominal):	0.235 in (5.97 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR
93.8 Ohm/km (28.6 Ohm/1000ft)

Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
538 ns/100m	45 ns/100m	67%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. SRL (Structural Return Loss) [dB]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	62.2	62.3	23	100 ± 15
4	4.1 dB/100m	53.3	53.3	23	100 ± 15
8	5.8 dB/100m	48.8	48.8	23	100 ± 15
10	6.5 dB/100m	47.3	47.3	23	100 ± 15
16	8.2 dB/100m	44.3	44.3	23	100 ± 15
20	9.3 dB/100m	42.8	42.8	23	100 ± 15
25	10.4 dB/100m	41.3	41.3	22	100 ± 15

31.25	11.7 dB/100m	39.9	39.9	21.1	100 ± 15
62.5	17.0 dB/100m	35.4	35.4	18	100 ± 15
100	22.0 dB/100m	32.2	32.3	16	100 ± 15

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

Operating
-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1 in (25 mm)	2.35 in (59.7 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	32 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
Data Category:	Category 5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1624R

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. RJ-45 Compatible. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5.
--------	--

History

Update and Revision:	Revision Number: 0.353 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1624P D151000	Blue	Reel	1,000 ft	612825119371	C
1624P D15A1000	Blue	Reel-in-Box	1,000 ft	612825119364	Z
1624P 0081000	Gray	Reel	1,000 ft	612825119456	C
1624P 008A1000	Gray	Reel-in-Box	1,000 ft	612825119449	Z
1624P 0051000	Green	Reel	1,000 ft	612825119425	C
1624P 8771000	Natural	Reel	1,000 ft	612825119470	Z C
1624P 877A1000	Natural	Reel-in-Box	1,000 ft	612825119463	Z
1624P 0031000	Orange	Reel	1,000 ft	612825119395	C Z
1624P 0071000	Purple	Reel	1,000 ft	612825119432	C
1624P 0021000	Red	Reel	1,000 ft	612825119388	C
1624P 0041000	Yellow	Reel	1,000 ft	612825119418	C
1624P 004A1000	Yellow	Reel-in-Box	1,000 ft	612825119401	Z

Footnote:	C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.