

**Product: [1673A](#)**


Conformable Coax, 50 Ohm, RG-402, 19 AWG Solid SCCS, Copper-Tin Composite Shield, Unjacketed

**Product Description**

Conformable Coax, 50 Ohm, RG-402, 19 AWG Solid Silvered Copper Covered Steel Conductor, PTFE Insulation, Copper Tape + 100% Tin-Filled Composite Braid Shield, Unjacketed

**Technical Specifications**
**Product Overview**

Suitable Applications: Microwave and other high frequency applications, Interconnect RF equipment, Radar equipment, Military communications

**Construction Details**

RG Type: 402

**Conductor**

Size	Stranding	Nom. Diameter	Material
19 AWG	Solid	0.036 in	SCCS - Silvered Copper Covered Steel

**Insulation**

Material	Nom. Insulation Diameter	Color Code
PTFE - Polytetrafluoroethylene	0.116 in (2.95 mm)	White

**Outer Shield**

Layer	Outer Shield Type	Material	Coverage	Notes
1	Tape	Bare Copper (BC)	100%	
2	Braid	Tinned Copper (TC + Tin Filled)	100%	Diameter: 0.138 inch

**Outer Jacket**

Material
No Jacket

Overall Cable Diameter (Nominal): 0.138 in (3.51 mm)

**Electrical Characteristics**
**VSWR**

Frequency	Max. VSWR
500 MHz	1.1:1
1000 MHz	1.11:1
3000 MHz	1.13:1
7000 MHz	1.17:1
15000 MHz	1.25:1
20000 MHz	1.3:1

VSWR Table Notes: VSWR limit is a continuous sloping line from 500 MHz to 20 GHz

**Attenuation**

Frequency	Nom. Attenuation
500 MHz	8.0 dB/100ft
1000 MHz	12.0 dB/100ft

3000 MHz	22.0 dB/100ft
5000 MHz	30.0 dB/100ft
10000 MHz	45.0 dB/100ft
20000 MHz	70.0 dB/100ft

#### Power Rating

Frequency	Max. Power Rating
500 MHz	600 W
1,000 MHz	401 W
2,000 MHz	268 W
3,000 MHz	211 W
5,000 MHz	157 W
7,000 MHz	129 W
10,000 MHz	105 W
15,000 MHz	83 W
18,000 MHz	74 W
20,000 MHz	70 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
20.5 Ohm/1000ft	4.5 Ohm/1000ft (15 Ohm/km)	29.5 pF/ft (96.8 pF/m)	50 Ohm	70%

#### Voltage

UL Voltage Rating	Voltage Rating
30 V (UL AWM Style 10245)	1900 V

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
105°C	-70°C to +200°C

##### Bend Radius

Installation Min.
0.250 in (6.35 mm)

Max. Pull Tension: 70 lbs (32 kg)

Bulk Cable Weight: 26 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1581 Horizontal Wire
AWM Compliance:	AWM 10245
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### History

Update and Revision: Revision Number: 0.477 Revision Date: 09-07-2025

#### Part Numbers

##### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1673A TIN50	Tin	Reel	50 ft	612825120407	
1673A TIN100	Tin	Reel	100 ft	612825120384	C
1673A TIN250	Tin	Reel	250 ft	612825120391	C V
1673A TIN500	Tin	Reel	500 ft	612825120414	

Footnote: C - CRATE REEL PUT-UP., V - 250' PUT-UP EXACT LENGTH MAXIMUM OF 3 PIECES, MINIMUM LENGTH 50'. 500' PUT-UP EXACT LENGTH MAXIMUM OF 5 PIECES, MINIMUM LENGTH 50'. 1000' PUT-UP EXACT LENGTH MAXIMUM OF 8 PIECES, MINIMUM LENGTH 50'.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.