

**Product: [1804A](#)**

REPRESENTATIVE IMAGE

Microphone Cable, Star Quad, 4 C #28 Str Silvered Copper Alloy, 80% TC Braid, PVC Jkt

**Product Description**

Microphone Cable, Star Quad, 4 Conductor 28 AWG (19 x 40) High Conductivity Silvered Copper Alloy, PP insulation, 80% Tinned Copper Braid Shield, PVC jacket

**Technical Specifications**
**Product Overview**

Suitable Applications: Microphone, Low Noise for high-EMI environments; Line level balanced analog audio

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	28 AWG	19x40	SCA - Silvered Copper Alloy (High Conductivity)

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.008 in (0.20 mm)	0.03 in (0.76 mm)	Blue, White, Blue/White Stripe, White/Blue Stripe

**Outer Shield**

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	80%

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.014 in (0.36 mm)	0.115 in (2.92 mm)

Overall Cable Diameter (Nominal): 0.115 in (2.92 mm)

**Electrical Characteristics**
**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	65 Ohm/1000ft	40 pF/ft (130 pF/m)	60 pF/ft (200 pF/m)	40 Ohm	0.21 $\mu$ H/ft (0.69 $\mu$ H/m)	66%	1.6 Amps per conductor @ 30°C

Nom Outer Shield DCR: 7.923 Ohm/1000ft (25.99 Ohm/km)

**Voltage**

Voltage Rating
100 V

**Mechanical Characteristics**
**Temperature**

UL Temperature	Operating
60°C	-30°C to +60°C

**Bend Radius**

Stationary Min.	Installation Min.
1.2 in (30 mm)	1.2 in (30 mm)

Max. Pull Tension: 9.2 lbs (4.2 kg)

Bulk Cable Weight: 9 lbs/1000ft

## Standards and Compliance

Environmental Suitability: Indoor (Not Riser or Plenum), Indoor

## Product Notes

Notes: Quad connection scheme: The two blue wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the two white wires (or remaining wires) are connected together to form the second conductor.

## History

Update and Revision: Revision Number: 0.492 Revision Date: 09-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1804A U4F500	Beige U4F	Reel	500 ft	612825123163	F
1804A J5C100	Black, Vivid Matte	Reel	100 ft	612825123149	
1804A J5C500	Black, Vivid Matte	Reel	500 ft	612825123156	F
1804A G8M500	Matte Yellow	Reel	500 ft	612825123132	F

Footnote: F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.