


**Product:** [1807A](#) 



S-Video, High-Flex, Dual Mini 75 Ohm #30 Coax, Parallel

## Product Description

S-Video Cable, 2-30 AWG stranded tinned copper coax, foam HDPE insulation, 90% tinned copper spiral serve shield, PVC jacket

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
30	7x38	TC - Tinned Copper	0.013 in	2

Conductor Count:

#### Insulation

Material
PE - Polyethylene (Foam)

#### Inner Shield

Type	Material	Coverage [%]
Spiral Serve / Screen	Tinned Copper (TC)	90%

#### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.230 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
100 Ohm/1000ft	100 Ohm/1000ft		7.5 Ohm/1000ft	7.5 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
17.3 pF/ft

#### Inductance

Nominal Inductance
0.097 $\mu$ H/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100ft
5 MHz	1.4 dB/100ft
10 MHz	2.1 dB/100ft

30 MHz	3.8 dB/100ft
50 MHz	5.1 dB/100ft
100 MHz	7.6 dB/100ft
200 MHz	11.3 dB/100ft
400 MHz	16.9 dB/100ft
700 MHz	23.3 dB/100ft
900 MHz	26.9 dB/100ft
1000 MHz	28.6 dB/100ft

#### Delay

<b>Nominal Velocity of Propagation (VP) [%]</b>
78%

#### Voltage

<b>Non-UL Voltage Rating</b>
300 V RMS

#### Temperature Range

Non-UL Temp Rating:	75°C
Operating Temperature Range:	-40°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	14 lbs/1000ft
Maximum Recommended Pulling Tension:	11.7 lbs
Minimum Minor Axis Bend Radius:	1 in

#### Standards

CPR Euroclass:	Eca
RG Type:	Ultra-miniature 59

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

#### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	7700A

#### Related Part Numbers

##### Variants

Item #	Color	Put-Up Type	Length	UPC
1807A B59500	Black, Matte	Reel	500 ft	612825357148
1807A B59U500	Black, Matte	UnReel	500 ft	612825357162
1807A B591000	Black, Matte	Reel	1,000 ft	612825357155
1807A B59U1000	Black, Matte	UnReel	1,000 ft	612825357179

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

#### History

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.