

**Product:** [1924A](#) 



Audio Snake Cable, #24-24pr, BC, Individ. Shielded

## Product Description

Audio Snake Cable, 24-24 AWG bare copper pairs, polyolefin insulation, individually shielded with double serve "French Braid", drain, numbered/color-coded PVC jackets, flexible PVC jacket

## Technical Specifications

### Product Overview

|                        |                                                                                                                                                          |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|

### Construction Details

#### Conductor

| Size | Stranding | Material         | No. of Pairs |
|------|-----------|------------------|--------------|
| 24   | 41x40     | BC - Bare Copper | 24           |

#### Insulation

| Material           | Nom. Insulation Diameter | Color Code                                                                                                                                                                                                                 |
|--------------------|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| PP - Polypropylene | 0.04 in (1.0 mm)         | Brown, Red, Orange, Yellow, Green, Blue, Purple, Gray, White, Black, Tan, Pink, Gray/Brown, Gray/Red, Gray/Orange, Gray/Yellow, Gray/Green, Gray/Blue, Gray/Purple, Gray/Gray, Gray/White, Gray/Black, Gray/Tan, Gray/Pink |
|                    |                          | Red and Black                                                                                                                                                                                                              |

#### Inner Shield

| Shield Type  | Material         | Coverage |
|--------------|------------------|----------|
| French Braid | Bare Copper (BC) | 95%      |

#### Inner Jacket

| Material                 | Nom. Diameter      |
|--------------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.119 in (3.02 mm) |

#### Outer Jacket

| Material                 | Nom. Diameter |
|--------------------------|---------------|
| PVC - Polyvinyl Chloride | 0.825 in      |

### Electrical Characteristics

#### Electricals

| Nom. Characteristic Impedance |
|-------------------------------|
| 60 Ohm                        |

#### Delay

| Nom. Velocity of Prop. |
|------------------------|
| 66%                    |

#### Voltage

| UL Voltage Rating |
|-------------------|
| 300 V RMS         |

Mechanical Characteristics

Temperature

| Operating          |                            |
|--------------------|----------------------------|
| -20°C To +60°C     |                            |
| Max. Pull Tension: | 700 lbs (320 kg)           |
| Bulk Cable Weight: | 397 lbs/1000ft (591 kg/km) |

Standards and Compliance

|                                |                                                                                                               |
|--------------------------------|---------------------------------------------------------------------------------------------------------------|
| Environmental Suitability:     | Indoor (Not Riser or Plenum), Indoor                                                                          |
| European Directive Compliance: | EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance:               | China RoHS II (GB/T 26572-2011)                                                                               |

History

|                      |                                                  |
|----------------------|--------------------------------------------------|
| Update and Revision: | Revision Number: 0.352 Revision Date: 09-07-2025 |
|----------------------|--------------------------------------------------|

Part Numbers

Variants

| Item #       | Color                  | Putup Type | Length | UPC          | Footnote |
|--------------|------------------------|------------|--------|--------------|----------|
| 192A B59TEST | Black, Matte           |            |        |              |          |
| 1924A B59500 | Black, Matte           | Reel       | 500 ft | 612825126898 | C        |
| Footnote:    | C - CRATE REEL PUT-UP. |            |        |              |          |

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.